



designed for scientists



RV 8 V-C

/// Data Sheet

The rotary evaporator RV 8 is the manual basic model in the family of IKA Rotation Evaporators. It finds a multitude of uses in the chemical, pharmaceutical, and biotechnology industries, in research and development, in manufacturing and quality assurance, in laboratories, and in plant construction. Thanks to specially designed glass guides, the vertical coated condenser makes extremely efficient use of the 1500 cm² cooling surface. Digital displays for speed and heating bath temperature enable optimum control of all distillation processes.

- heating bath with 4 l volume
- integrated safety lift-out function in case of power failure



designed for scientists

- package includes Woulff bottle
- water/oil heating bath with carrying handles
- locking button for fixing heating bath temperature
- clearly legible, glass-covered, black-and-white display panel
- locking mechanism: red indicator shows unlocked position of the vapor tube
- manual lift for precise positioning of the glassware
- adjustable immersion angle
- single-handed manual lift handling, suitable for left and right-handed operators
- speed range: 5 - 300 min⁻¹
- low device voltage (24V) ensures user safety
- flask clamping mechanism with integrated push-off function for easy exchange of evaporation flasks
- high-efficiency condenser with 1500 cm² cooling surface - low space requirements
- compatible with the entire range of IKA RV 10 glassware

Scope of delivery

- RV 8 drive
- HB digital S099
- RV 10.10 Glassware vertical coated
- RV 10.88 Clamp NS 29
- RV 10.70 Vapor tube (NS 29/32)
- RV 10.8001 Seal
- RV 3.4 Woulff bottle



designed for scientists

Technical Data

Speed range [rpm]	5 - 300
Speed display	LED
Speed tolerance set rotation speed < 100rpm [rpm]	±1
Speed tolerance set rotation speed > 100rpm [%]	±1
Lift	manual
Stroke [mm]	120
Dimensions (W x H x D) [mm]	615 x 595 x 390
Weight [kg]	26.07
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 20
Voltage [V]	100 - 240
Frequency [Hz]	50/60
Power input [W]	75